

50.8mm Dia. x 50mm FL, Uncoated, ISP Optics Germanium (Ge) Meniscus Lens | GE-PM-50-50

See More by [ISP Optics](#)



Stock **#24-837** 3-4 DAYS

- 1 + **£584.80**

ADD TO CART

Qty 1-5
£584.80

Qty 6+
£467.84

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
50.80 +0.00/-0.13

Effective Focal Length EFL (mm):
50.00 @ 10.6µm

Substrate: <a>Germanium (Ge)
f/#: 0.98
Numerical Aperture NA: 0.51
Coating: Uncoated
Type: Meniscus Lens
Wavelength Range (nm): 2000 - 14000
Center Thickness CT (mm): 5.20 ±0.20
Centering (arcmin): <3
Clear Aperture (%): 90
Clear Aperture CA (mm): 45.72
Edge Thickness ET (mm): 3.10
Focal Length Tolerance (%): ±2
Model Number: GE-PM-50-50
Radius R₁ (mm): 65.77
Radius R₂ (mm): 48.53
Surface Quality: 60-40
Irregularity (P-V) @ 10.6µm: λ/20

Regulatory Compliance

RoHS 2015: <a>Compliant
Certificate of Conformance: <a>View