

TECHSPEC[®] 50.8mm Dia. x 9.53mm 532/630-655/1064nm, Dual Band Laser Mirror



Stock #26-928 12 In Stock

-

1

+

£278^{.41}

ADD TO CART

Volume Pricing	
Qty 1-5	£278.41 each
Qty 6-25	£264.40 each
Qty 26-49	£250.39 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Laser Mirror

Type:

Physical & Mechanical Properties	
<3	Parallelism (arcmin):
>90	Clear Aperture (%):
Commercial Polish	Back Surface:
50.80 +0/-0.1	Diameter (mm):
9.53 ±0.10	Thickness (mm):
Optical Properties	
10-5	Surface Quality:
99.5	Reflection at DWL (%):
R _{avg} ≥99.50% @ 532nm & 1064nm @ 45° AOI R _{avg} ≥80% @ 630 – 655nm @ 45° AOI	Coating Specification:
λ/10	Surface Flatness (P-V):
Dielectric	Coating Type:
Laser Mirror (532, 635, 650, 1064nm)	Coating:
532, 635, 650, 1064	Design Wavelength DWL (nm):
45	Angle of Incidence (°):
Fused Silica (Corning 7980)	Substrate:
Not Specified	Damage Threshold, Reference:

Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- >99% Reflectivity at Design Wavelengths
 - 10-5 Surface Quality for Sensitive Laser Applications
 - 532/1064nm, 635-670/1064nm, or 800/1030nm Wavelength Bands
 - [TECHSPEC® Nd:YAG Laser Line Mirrors](#) Also Available
- TECHSPEC® Dual Band Laser Line Mirrors feature high reflectivity, excellent surface quality, and precision surface flatness to minimize scattering effects. Each coating design has been tested to ensure a high laser damage threshold for compatibility with pulsed laser systems. These fused silica substrate laser mirrors have excellent thermal stability and are available in a variety of standard sizes. TECHSPEC® Dual Band Laser Line Mirrors are ideal for beam steering applications in both laboratory and OEM laser systems. These mirrors are available in a 532/1064nm, 635-670/1064nm, and 800/1030nm dual band coating options for Nd:YAG lasers and red and green guide beams.