

TECHSPEC® 50mm Dia., VIS-NIR Coated, 30' Wedge, Fused Silica Wedged Window



TECHSPEC® Fused Silica Wedged Windows

Stock **#17-668** 3-4 DAYS



1



£221.00

ADD TO CART

Qty 1-5

£221.00

Qty 6+

£176.80

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Clear Aperture CA (mm):
45.00

Diameter (mm):
50.00 +0.0/-0.10

Thickness (mm):
3.00 ±0.20

Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 0.52 (+5 to +35°C) 0.57 (0 to +200°C) 0.48 (-100 to +200°C)
Edges: Fine Ground
Index of Refraction n_d: 1.458
Substrate:  Fused Silica (Corning 7980)
Surface Flatness (P-V): λ/10 over 25mm Aperture
Surface Quality: 20-10
Type: Wedged Window
Wavelength Range (nm): 400 - 1000
Young's Modulus (GPa): 73
Wedge Angle: 30' ±10'
Damage Threshold, Reference:  5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant