

TECHSPEC® 50mm Dia x -50mm FL, Protected Aluminum, Convex Mirror



Convex Mirrors

Stock **#87-662** 3-4 DAYS

⊖ 1 ⊕ **£53.55**

ADD TO CART

Qty 1-5
£53.55

Qty 6+
£42.92

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
50.00

Focal Length FL (mm):
-50.00

Center Thickness CT (mm):
5.00

Clear Aperture (%): 90.00
Coating: Protected Aluminum (400-700nm)
Coating Specification: R_{avg} >85% @ 400 - 700nm
Coating Type: Metal
Dimensional Tolerance (mm): +0.0/-0.1
Edge Thickness ET (mm): 1.83
Focal Length Tolerance (%): ±2
Radius R (mm): 100.0
Substrate: N-BK7
Surface Accuracy: λ/2
Surface Quality: 60-40
Thickness Tolerance (mm): ±0.1
Type: Spherical Mirror
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant