


TECHSPEC[®] 50mm Diameter Uncoated, Ultra-Thin N-BK7 Window

See More by [SCHOTT Optical Components](#)



Ultra-Thin N-BK7 Windows

Stock **#66-191** 3-4 DAYS



1



£146.63

ADD TO CART

Qty 1-5

£146.63

Qty 6+

£117.30

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Abbe Number (v_d):
64.17

Bevel:
Protective as needed

Clear Aperture CA (mm):

45.00
Diameter (mm): 50.00 +0.00/-0.10
Thickness (mm): 0.20 ±0.025
Coating: Uncoated
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 7.1 (-30 to +70°C) 8.3 (+20 to +300°C)
Density (g/cm³): 2.51
Edges: Fine Ground
Index of Refraction n_d: 1.516
Knoop Hardness (kg/mm²): 610
Parallelism (arcsec): <30
Poisson's Ratio: 0.206
Substrate: N-BK7
Surface Quality: 40-20
Transmitted Wavefront, P-V: λ/2
Type: Protective Window
Wavelength Range (nm): 350 - 2200
Young's Modulus (GPa): 82

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View