

36mm Max. Aperture, Stainless Steel Iris Diaphragm



Stock #64-505 3-4 DAYS

- 1 + **£81.60**

ADD TO CART

Qty 1-4
£81.60

Qty 5+
£72.33

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
1.9

Maximum Aperture (mm):
36.0

Outer Diameter (mm):

50.0
Construction: Blackened Aluminum Housing, Stainless Steel Leaves
Lever Diameter (mm): 3.00
Lever Length (mm): 12.50
Number of Leaves: 16.00
Thickness (mm): 6.00

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 235: Contains SVHC(s)
