

50µm Aperture Diameter, Mounted, Precision Pinhole



50µm Aperture Diameter, Mounted, Precision Pinhole, #56-282

Stock **#56-282** ☐ In Stock

-

1

+

£63.75

ADD TO CART

Qty 1-5
£63.75
Qty 6+
£56.27
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type: Mounted
Outer Diameter (mm): 25 +0.4/-0.000
Construction: Stainless Steel

Fixed Aperture Diameter (μm): 50
Thickness (mm): 0.03 Nominal
Aperture Tolerance (μm): ±5
Mount Thickness (mm): 1.25 ±0.05
Aperture Centration (μm): ±125

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant