

51 x 76mm, 40R/60T, Plate Beamsplitter



Stock #46-676 3-4 DAYS

-

1

+

£68.85

ADD TO CART

Qty 1-9
£68.85
Qty 10+
£51.00
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating Specification:
Surface 1: Dielectric, ±5% R/T @ 550nmSurface 1:
Dielectric, ±5% R/T @ 550nm
Surface 2: N4 MgF₂ @ 550nm

Construction:
Plate

Dimensional Tolerance (mm):

±0.38
Dimensions (mm): 51.0 x 76.0
Edges: Cut
Reflection/Transmission Ratio (R/T): 40/60
Substrate: ☐ Float Glass
Surface Flatness (P-V): 4 - 6λ
Surface Quality: 80-50
Thickness (mm): 3.00
Type: Standard Beamsplitter
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant