See all 11 Products in Family

51.5mm Diameter Float Glass Window



Stock **#44-063** **20+ In Stock**

- 1 + **£14.80**

ADD TO CART

Volume Pricing	
Qty 1-5	**£14.80** each
Qty 6-49	**£13.60** each
Qty 50-99	**£12.00** each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:
Protective Window

Physical & Mechanical Properties

Bevel:
Protective as needed

Diameter (mm):
51.50

Thickness (mm):

1.50

Edges:

Fine Ground

Optical Properties

Coating:

Uncoated

Substrate:

Float Glass

Surface Flatness (P-V):

4 - 6λ

Surface Quality:

80-50

Wavelength Range (nm):

350 - 2000

Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

View

Reach 247:

Compliant

Product Details

- Transmits Visible and Near Infrared Wavelengths
- Available Uncoated or with an Anti-Reflection Coating
- Variety of Sizes Available

Float Glass Optical Windows are optical glass with polished faces that are relatively parallel and are typically used as a protective element between two environments. Float glass readily transmits visible and near-infrared wavelengths and can be used in a wide variety of applications. Float Glass Optical Windows are versatile products offered in circular and rectangular options. They are available uncoated or with BBAR (Broadband Anti-Reflective) 400-700nm coating.

Compatible Mounts