

532nm, 25.4mm Dia., Top-Hat Diffractive Beam Shaper



HOLO/OR Diffractive Beam Shapers

Stock #14-680 3-4 DAYS

- 1 + **£3,936.35**

ADD TO CART

Qty 1+
£3,936.35

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Clear Aperture CA (mm):
22.9

Coating:
Laser V-Coat (532nm)

Design Wavelength DWL (nm):
532

Diameter (mm):
25.40 +0.05/-0.15

Substrate: Fused Silica (Corning 7980)
Thickness (mm): 3.00 ±0.1
Input Beam Mode: SMTEM ₀₀ , M ² <1.5
Output Shape: Square
Full Angle At 1/e² (mRad): 0.38
Transfer Region (mRad): 0.10
Overall Efficiency (%): 95
Input Beam Diameter, 1/e² (mm): 5
Damage Threshold, Reference: ☐ See Link for More Details

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant