

TECHSPEC® 5mm Aluminum & UV-VIS, Ultra Precision UV Fused Silica Right Angle Prism



Stock **#39-840** [CONTACT US](#)



1



£227.80

ADD TO CART

Qty 1-5

£227.80

Qty 6+

£205.02

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle Tolerance (arcsec):
±15

Coating:
UV-VIS & Aluminized

Substrate: ☐
[Fused Silica](#) (Coming 7980)

Surface Quality: 20-10
Type: Right Angle Prism
Dimensional Tolerance (mm): +0.00/-0.10
Bevel: Protective bevel as needed
Clear Aperture (%): 90
Length of Hypotenuse (mm): 7.10
Length of Legs (mm): 5.00
Pyramid Tolerance (arcmin): ±1
Image Orientation: Left-Handed
Coating Specification: Legs: R_{abs} ≤1.0% @ 350 - 450nm, R_{avg} ≤1.5% @ 250 - 700nm Hypotenuse: R_{avg} >85% @ 400 - 700nm, R_{avg} >90% @ 400 - 2000nm w/Black Overpaint
Wavelength Range (nm): 250 - 700
Surface Flatness (P-V): λ/20
Damage Threshold, By Design: ☐ Hypotenuse: 0.3 J/cm² @ 532 & 1064nm, 10ns Legs: 3 J/cm² @ 355nm, 10ns; 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant