

TECHSPEC® 5mm N-SF11 Uncoated Equilateral Prism



Equilateral Prisms

Stock **#49-430** **20+ In Stock**

⊖ 1 ⊕ £82.40

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-5 | £82.40 each |
| Qty 6-25 | £66.00 each |
| Qty 26-49 | £61.80 each |
| Need More? | Request Quote |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Equilateral Prism **Type:**

Physical & Mechanical Properties

5.00 **Length of Face (mm):**

Length (mm):

5.00

Dimensional Tolerance (mm):

±0.1

Optical Properties

Coating:

Uncoated

Substrate:

[N-SF11](#)

Surface Quality:

40-20

Angle Tolerance (arcmin):

±2

Image Orientation:

Dispersion

Wavelength Range (nm):

400 - 2500

Power (fringes) @ 632.8nm:

2.50

Irregularity (fringes) @ 632.8nm:

0.50

Regulatory Compliance

Certificate of Conformance:

[View](#)

Product Details

- Ideal for Light Dispersion
- Sizes Ranging from 5 - 50mm
- Available Uncoated or Anti-Reflection Coated
- Additional [Equilateral Prism](#) Options Available

TECHSPEC® Equilateral Prisms feature three equal 60° angles and are often referred to as dispersing prisms. Equilateral prisms are ideal for wavelength separating applications and light dispersion. These prisms are available in sizes ranging from 5-50mm. Our TECHSPEC® Equilateral Prisms are offered uncoated or with a single layer MgF2 anti-reflection coating. Additional [Equilateral Prism](#) options are available.

Technical Information

