


5mW, 635nm Laser Bat Power ZAT, 60° X-Hair



Stock **#19-540** [CONTACT US](#)



1



£255.00

ADD TO CART

Qty 1-9

£255.00

Qty 10+

£229.50

Volume Pricing

Get Product Downloads



Output Power (mW): 5
Wavelength (nm): 635.00
Weight (g): 162
Power Requirement: 1 AA Battery (Not Included)
Style: Crosshair
Output Type: Free Space
Laser Class - CDRH: 1M
Color: Red
Fan Angle (°): 60.00
Focus Range: Up to 1,500mm
Length (mm): 124.00
Environmental Rating: IP40

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View