

TECHSPEC® 5X Arcturus® HeNe Beam Expander



5X HeNe Fixed Beam Expander, #55-577

Stock #55-577 3-4 DAYS

1 **£403.75**

ADD TO CART

Qty 1-4

£403.75

Qty 5+

£356.15

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle of Incidence (°):
0

Coating:
BBAR (450-750nm)

Design Wavelength DWL (nm):
633

Entrance Aperture (mm): 2
Exit Aperture (mm): 27
Expansion Power: 5X
Focus Range: 1.2m - ∞
Substrate: ☐ Optical Glass
Length (mm): 107.50
Mounting Threads: C-Mount
Type: Beam Expander
Weight (g): 409
Housing Diameter (mm): 50
Transmitted Wavefront, P-V: <λ/4 @ 633nm for Input Beam ≤1mm
Coating Specification: R_{abs} <0.4% @ 630 - 670nm R_{avg} <0.6% @ 450 - 750nm
Wavelength Range (nm): 450 - 750
Style: Fixed Magnification
Divergence Adjustment: Non-Rotating Optics

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View