

6", IR 850nm, UltraSeal Washdown Bar Light

See More by [Advanced Illumination](#)



Advanced Illumination UltraSeal Washdown Bar Lights

Stock **#18-627** 3-4 DAYS

- 1 +

£720.80

ADD TO CART

Qty 1+

£720.80

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Color:
IR

Input Voltage (V):
24V

Model Number:
AL247M06-850IC

Operating Temperature (°C):
0 - 60

Dimensions (mm): 171.4 x 42.9 x 24
Wavelength (nm): 850.00
Weight (g): 417
LED Lifetime (hours): 50000
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Type of Illumination: LED Illuminator
Note: Optional Manual Intensity Adjustment #86-887 and #89-555 are Available
Manufacturer: Advanced Illumination
Geometry: Area Light
Illumination Mode: Constant
Environmental Rating: IP69K
Minimum Input Current: 0.20A

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 233: Contains SVHC(s)
