

TECHSPEC®

6.0mm Dia. x -9 FL, VIS-NIR, UV Plano-Concave Lens



UV Fused Silica Plano-Concave (PCV) Lenses



Stock **#21-043** [CONTACT US](#)

[Other Coating Options](#)



1



£112.20

ADD TO CART

Qty 1-5

£112.20

Qty 6+

£89.67

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
6.00 +0.0/-0.025

Effective Focal Length EFL (mm): -9.00
Substrate: Fused Silica (Coming 7980)
f/#: 1.5
Numerical Aperture NA: 0.33
Coating: VIS-NIR (400-1000nm)
Type: Plano-Concave Lens
Wavelength Range (nm): 400 - 1000
Back Focal Length BFL (mm): -10.38
Center Thickness CT (mm): 2.00
Center Thickness Tolerance (mm): ±0.05
Centering (arcmin): <3
Clear Aperture CA (mm): 5.4
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Edge Thickness ET (mm): 3.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Note: Max. Flat Annulus is 0.3mm
Radius R ₁ (mm): -4.13
Surface Quality: 40-20
Damage Threshold, Reference: 5 J/cm² @ 532nm, 10ns
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant