

TECHSPEC[®] 6.25mm Dia x -50mm FL VIS 0° Coated, Illumination Grade PCV Cylinder Lens



TECHSPEC[®] Illumination Grade PCV Cylinder Lenses

Stock #69-793 3-4 DAYS

-

1

+

£67.58

ADD TO CART

Qty 1-5

£67.58

Qty 6+

£53.98

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
6.25 +0.0/-0.2

Effective Focal Length EFL (mm):
-50.00

Substrate: ☐
[N-BK7](#)

f/#: 8.00
Numerical Aperture NA: 0.06
Coating: VS 0° (425-675nm)
Type: Cylinder Lens, Plano-Concave
Wavelength Range (nm): 425 - 675
Back Focal Length BFL (mm): -51.32
Center Thickness CT (mm): 2.00
Center Thickness Tolerance (mm): ±0.1
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Edge Thickness ET (mm): 2.19
Focal Length Tolerance (%): ±3
Radius R₁ (mm): -25.84
Surface Quality: 60-40
Damage Threshold, Reference: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant