

625nm, High Intensity Coaxial Spot Light

See More by [Advanced Illumination](#)



Advanced Illumination High Intensity Coaxial LED Spot Light Illuminator

Stock #11-028 3-4 DAYS



1



£522.75

ADD TO CART

Qty 1+

£522.75

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color:
Red

Model Number:
SL162-625IC

Operating Temperature (°C):
0 to 60

Weight (g): 85.1
LED Lifetime (hours): 50,000
Power Supply: Power Supply Required and Sold Separately: USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Number of LEDs: 1
Length of Cable (m): 2
Type of Illumination: LED Illuminator
Manufacturer: Advanced Illumination
Geometry: Spot Light
Illumination Mode: Constant

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 233: Contains SVHC(s)
