

TECHSPEC® 632.8nm, 12.5mm Diameter, OD 4.0 Notch Filter



TECHSPEC OD 4.0 Notch Filters

Stock **#67-111** 3-4 DAYS

[Additional Bandwidths](#)



1



£242.25

ADD TO CART

Qty 1-5

£242.25

Qty 6+

£190.40

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50 +0.00/-0.10

Optical Density OD (Average):
≥4.0

Clear Aperture CA (mm):

10.6
Center Wavelength CWL (nm): 632.80
Design Wavelength DWL (nm): 632.8
Full Width-Half Max FWHM (nm): 31.60
Coating: Hard Coated
Surface Quality: 60-40
Thickness (mm): 5.00
Thickness Tolerance (mm): ±0.1
Transmission (%): 90
Transmission Wavelength (nm): 475 - 845
Type: Notch Filter
Construction: Mounted in Black Anodized Ring
Reflection at CWL (%): 99
Transmitted Wavefront, RMS: <1λ
Environmental Durability: Humidity per MIL-STD-810H, Section 507.6 Temperature per MIL-STD-810H, Section 501.7 and 502.7
Physical Durability: Adhesion per MIL-PRF-13830B, Section C.4.5.12 Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11 Cleaning per MIL-C-48497A Section 4.5.4.2
Mount Thickness (mm): 5.0
Substrate Thickness (mm): 3.5 ±0.5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant