

7" Diagonal LCD Flat Panel Monitor



Stock **#35-128** CLEARANCE CONTACT US

- 1 + **£144.46**

ADD TO CART

Qty 1+
£144.46

Volume Pricing
Request Quote

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type: Monitor
Resolution (MegaPixels): 0.50
Power Supply: 100 - 240 VAC Included
Power Consumption (W): 7.5
Dimensions (mm): 179.6 x 120 x 23

Weight (g): 870
Dot Pitch (mm): 0.135 x0.416
Size of Screen, Diagonal (inches): 6.4
Resolution: 1440 x234
Maximum Viewing Angle, MVA(°): Left/Right/Down 70, Up 50
Input/Output Options: Mini Phone Jack (RCA Adapter Included)
Active Area (mm): 154.08 x86.58
Signal Format: NTSC/ PAL
Contrast: 400:1 (typical)
Brightness (cd/m²): 400
Response Time (ms): Tr: 12ms Tf: 18ms
Safety Standards: FCC Class B
Video Input: NTSC/PAL

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View