

640nm CWL, 10nm FWHM, 25mm Mounted Diameter



Stock #65-713 3-4 DAYS

- 1 + **£140.25**

ADD TO CART

Qty 1-9
£140.25

Qty 10+
£126.06

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Diameter (mm):
25.00 +0.0/-0.2

Angle of Incidence (°):
0

Optical Density OD (Average):
≥3.0

Clear Aperture CA (mm): 21.0
Center Wavelength CWL (nm): 640.00 ±2
Center Wavelength CWL Tolerance (nm): ±2
Full Width-Half Max FWHM (nm): 10.00 ±2
Full Width-Half Max FWHM Tolerance (nm): ±2
Minimum Transmission (%): ≥45
Operating Temperature (°C): -50 to +75
Coating: Traditional Coated
Surface Quality: 80-50
Thickness Tolerance (mm): ±0.1
Type: Bandpass Filter
Typical Applications: Ne Emission Line
Blocking Wavelength Range (nm): 200 - 1200
Construction: Mounted in Black Anodized Ring
Mount Thickness (mm): 7.5 ±0.1

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View