

## 6.96mm FL, High Resolution, f/1.6, Micro Video Lens



Stock **#17-160** [CONTACT US](#)

-

1

+

£62.90

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-49                      |
| £62.90                        |
| Qty 50+                       |
| £48.45                        |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length (mm):  
29.60

Maximum Diameter (mm):  
19

Maximum Image Circle (mm):  
8.00

Note:

|                                          |
|------------------------------------------|
| High Resolution                          |
| <b>Type:</b><br>M12 Imaging Lens         |
| <b>Focal Length FL (mm):</b><br>6.96     |
| <b>Maximum Sensor Format:</b><br>1/2"    |
| <b>Working Distance (mm):</b><br>400 - ∞ |
| <b>Mount:</b><br>M12 x0.5 (S-Mbunt)      |
| <b>Aperture (f/#):</b><br>f/1.6          |
| <b>IR Cut Filter:</b><br>No              |
| <b>Lens Wavelength Range:</b><br>VIS     |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
|------------------------------------------------------------|