

TECHSPEC® 6mm Aperture x 75mm L Standard NA, Fused Silica Light Pipe



Fused Silica Light Pipe Homogenizing Rods



Stock **#63-095** 3-4 DAYS

- 1 +

£170.00

ADD TO CART

Qty 1-5
£170.00
Qty 6+
£136.00
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:

Uncoated

Substrate:

[Fused Silica](#) (Corning 7980)

Length (mm):
75.00

Surface Quality:
60-40

Type:
Light Pipe

Entrance and Exit Aperture (mm):
6.00

Parallelism (arcmin):
5.00

Length Tolerance (mm):
±0.3

Aperture Tolerance (mm):
±0.10

Image Orientation:
Light Homogenization

Light Source NA:
Standard

Wavelength Range (nm):
200 - 2200

Surface Flatness (P-V):
1λ

#Sorting:
40.00

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Reach 209:
[Compliant](#)

Certificate of Conformance:
[View](#)