

TECHSPEC® 6mm Dia x 12mm FL VIS 0° Coated, Illumination Grade PCX Cylinder Lens



Stock #69-714 3-4 DAYS

-

1

+

£67.58

ADD TO CART

Qty 1-5
£67.58
Qty 6+
£53.98
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
6.00

Effective Focal Length EFL (mm):
12.00

Substrate: ☐

N-BK7

f/#: 2
Numerical Aperture NA: 0.25
Coating: VIS 0° (425-675nm)
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 425 - 675
Back Focal Length BFL (mm): 10.55
Center Thickness CT (mm): 2.20
Center Thickness Tolerance (mm): ±0.1
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Dimensional Tolerance (mm): +0.0/-0.2
Edge Thickness ET (mm): 1.43
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 6.20
Surface Quality: 60-40
Damage Threshold, Reference: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant