

TECHSPEC® 6mm Dia x 18mm FL VIS 0° Coated, Illumination Grade PCX Cylinder Lens



Stock **#69-715** 3-4 DAYS

- 1 + **£67.58**

ADD TO CART

Qty 1-5
£67.58

Qty 6+
£53.98

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
6.00

Effective Focal Length EFL (mm):
18.00

Substrate: ☐
N-BK7

f/#: 3
Numerical Aperture NA: 0.17
Coating: VIS 0° (425-675nm)
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 425 - 675
Back Focal Length BFL (mm): 16.81
Center Thickness CT (mm): 1.80
Center Thickness Tolerance (mm): ±0.1
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Dimensional Tolerance (mm): +0.0/-0.2
Edge Thickness ET (mm): 1.30
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 9.30
Surface Quality: 60-40
Damage Threshold, Reference: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant