

75mm Focal Length Lens, 1" Sensor Format



75mm Focal Length Lens, 1" Sensor Format, #63-249

Stock **#63-249** **5 In Stock**

-

1

+

£609⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£609.00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

1" Format Fixed Focal Length Lenses

Series:

Fixed Focal Length Lens

Type:

Physical & Mechanical Properties

Variable

Iris Option:

Length (mm):

57.00	
48.0	Maximum Diameter (mm):
48	Outer Diameter (mm):
180	Weight (g):

Optical Properties	
9.7°	Horizontal Field of View, 1" Sensor:
16.00	Maximum Image Circle (mm):
<-0.2	TV Distortion (%):
75.00	Focal Length FL (mm):
1,000 - ∞	Working Distance (mm):
f/1.8 - f/16	Aperture (f/#):
<-0.2%	Maximum Distortion (%):
VIS	Lens Wavelength Range:

Sensor	
1"	Maximum Sensor Format:
5.00	Pixel Size (µm):

Threading & Mounting	
M46 x0.75	Filter Thread:
C-Mount	Mount:

Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	REACH 241:

Product Details

- Up to 1", C-Mount Lens
- "Fast" Lenses for Increased Throughput
- 4.7mm to 75mm Focal Length

1" Format Fixed Focal Length Lenses provide high throughput and high resolution across the entire camera sensor, allowing for excellent imaging even in less-than-ideal lighting conditions. Offered in 9 focal lengths from 4.7mm to 75mm, this complete family covers many of the applications in the market today. Engineered to minimize distortion, these lenses provide a perfect image for a human operator or an automated system. 1" Format Fixed Focal Length Lenses also feature a standard C-Mount lens mount for easy integration with the most common machine vision [cameras](#) we offer. All lenses feature front filter threading to attach to your choice of [optical filter](#).