

7mm Heavy Duty Clamp



7mm Heavy Duty Clamp

Stock **#72-826** **1 In Stock**

⊖ 1 ⊕ £78.⁰⁰

ADD TO CART

Volume Pricing

Qty 1-9	£78.00 each
Qty 10+	£74.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads



Regulatory Compliance

Compliant RoHS 2015:

[View](#) Certificate of Conformance:

Compliant Reach 240:

Product Details

- 7mm Housing Diameter
- Focusable
- Low Voltage DC Operation
- Reverse Polarity Protection

Micro LDMLaser Diode Modules feature an extremely compact design that includes automatic power control circuits and focusable optics. The rugged body is low voltage isolated from the drive electronics, removing the need for negative or floating supplies. It has a highly visible red laser output that can be seen in most daylight conditions. Micro LDMLaser Diode Modules' additional features include aspheric lens, elliptical beam, small output beam diameter, and focused spot size. Meet IEC60825 certification, in accordance with CDRH. Applications include alignment/positioning, bar code readers, dimensional scanning, metrology, event detection, robot control, target designation, edge detection, analysis, and security.

Recommended power supply: [#59-099](#)

;