

TECHSPEC[®] 8" Diameter x 48" FL Uncoated, Parabolic Mirror



Stock #32-074-000 3-4 DAYS

-

1

+

£716.55

ADD TO CART

Qty 1-2
£716.55
Qty 3+
£609.45
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Substrate:

BOROFLOAT[®]SUPREMAX[®]

Focal Length Tolerance (%):
±1.5

Surface Quality:
60-40

Surface Accuracy:

N/8
Diameter (inches): 8.0 +0.06/-0
Diameter (mm): 203.20 +1.5/-0
Effective Focal Length EFL (inches): 48.0
Effective Focal Length EFL (mm): 1,219.20
Radius of Curvature (mm): 2,438.40
Aperture (f/#): f/6
Coating: Uncoated
Coating Type: Uncoated
Back Surface: Ground
Clear Aperture CA (mm): 183
Edge Thickness ET (inches): 1.37
Edge Thickness ET (mm): 34.80
Type: Parabolic Mirror

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View