

[See all 53 Products in Family](#)

8-pin GPIO Cable, IP65/67, 10m

See More by [IDS Imaging Development Systems](#)



Stock #19-689 [CONTACT US](#)

⊖ 1 ⊕ £172.⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	£172.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Camera Accessory **Type:**

Note:
8-pin Binder Connector to open end: 6 wires for Trigger and Flash, 2 wires for power

Hardware & Interface Connectivity

Length of Cable (m):
10

8-pin Binder Connector

Connector:

Regulatory Compliance

[Compliant](#)

RoHS 2015:

[View](#)

Certificate of Conformance:

[Compliant](#)

REACH 241:

Product Details

- Designed for Harsh Environments
- Robust IP65/67 Housing for Dust and Washdown Protection
- Compatible with [TECHSPEC® Cw Series Lenses](#)
- IP65/67 Rated Accessories and Illumination Also Available

IDS Imaging uEye+ FA IP65/67 PoE Cameras feature robust IP65/67 rated housings to withstand harsh industrial environments, providing protection against dirt, dust, and water. These cameras provide plug-and-play functionality and require no additional enclosures when paired with [TECHSPEC® Cw Series Lenses](#). Featuring IP65/67 rated accessories, these cameras utilize IDS Imaging's latest Peak SDK platform that supports GenICam and GigE Vision standards, simplifying system integration and software development. IDS Imaging uEye+ FA IP65/67 PoE Cameras are ideal for a wide variety of demanding applications requiring washdown and dust resistance including factory automation, medical technology, and machine vision.

;