

80mm, Metric Rotary Stage



60mm Dia. Precision Rotary Stage, #55-029



Stock **#62-294** [CONTACT US](#)

-

1

+

£254⁷⁷

£424.62

ADD TO CART

Volume Pricing	
Qty 1-4	£424.62 £254.77 each
Qty 5+	£375.15 £225.09 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Type:

Metric	
Physical & Mechanical Properties	
Rotary	Type of Movement:
Slide-Fit	Guide System:
80 Dia.	Stage Size (mm):
±5 (Fine), 360 (Coarse)	Travel (°):
M16 x 1	Center Hole:
20	Concentricity (µm):
Aluminium Stage	Construction:
5'	Increments:
6	Load Capacity (kg):
39.0	Travel Per Knob Rotation (arcmin):
0.5	Weight (kg):

Hardware & Interface Connectivity

Metric Micrometer	Type of Drive:
-------------------	----------------

Threading & Mounting

(1) M16 x 1, (12) M4 x0.7	Mounting Threads:
---------------------------	-------------------

Regulatory Compliance

Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 247:

PRODUCT DETAILS

- Precision Micrometer Drive and Manual Drive Options
- 360° Coarse Rotation
- Micrometer Drive Models Provide ±5° Fine Rotation
- Black Anodized Aluminum Construction

Metric Rotary Stages feature slide-fit guide system, enabling 360° course rotation. Micrometer drive models feature a precision metric micrometer and a switchable clamp mechanism to change between course and fine movements for precise ±5° angular adjustment at any position. The manual drive model provides a smooth manual adjustment with 360° coarse movement, 1° increments . Metric Rotary Stages feature a locking mechanism to fix the stage position. For breadboard mounting, use the [Metric Base Plates](#).

TECHNICAL INFORMATION

