

850nm 225mm Compact Light w/ Multi-Drive™



225mm Compact Light



Stock **#23-947** 1 In Stock

-

1

+

£1,116⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£1,116.00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
JWL225-MD-850	Model Number:
LED Illuminator	Type of Illumination:
Smart Vision Lights LLC	Manufacturer:

Ring Light	Geometry:
Constant or Strobed	Illumination Mode:
Physical & Mechanical Properties	
230 W x 142 H x 45D (60.40 D Including Connector)	Dimensions (mm):
1496.85	Weight (g):
144.50W x 56.5H	Active Area (mm):
Optical Properties	
IR	Color:
850	Wavelength (nm):
500 - 2,000	Working Distance (mm):
Electrical	
30 - ∞	Strobe Duration (µs):
Hardware & Interface Connectivity	
5-pin M12 connector	Connector:
24 VDC ± 5%	Input Voltage (V):
Threading & Mounting	
T-Slot for M6 Nut	Mount:
Environmental & Durability Factors	
-10° to +40°	Operating Temperature (°C):
IP65	Environmental Rating:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Direct Connect and Control via Camera's Trigger Output
- Built-In Multi-Drive™ Technology
- T-Slots for Mounting

Smart Vision Lights Compact Ring Lights are IP65-rated brightfield lights featuring a working distance of 500-mm to 2000-mm that can be directly connected to a camera for control via the trigger output. Built-in Multi-Drive™ technology, which offers both continuous operation and OverDrive™ mode, delivers up to 6 times the continuous power with a low-latency response and fast strobe durations down to 10mS. These lights feature a batwing design that illuminates a larger area than built-in lighting systems and produces a greater light output making them ideal to use alongside polarizers, diffusers, and other optical elements that reduce light output. Smart Visions Lights Illumination products offer an industry-leading 10-year limited warranty.