

890nm CWL, 10nm FWHM, 12.5mm Mounted Diameter



Stock **#67-789** 3-4 DAYS

- 1 + **£75.65**

ADD TO CART

Qty 1-9
£75.65

Qty 10+
£68.25

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Diameter (mm): 12.50 +0.00/-0.25
Angle of Incidence (°): 0
Optical Density OD (Average): ≥4.0

Clear Aperture CA (mm): 9.0
Center Wavelength CWL (nm): 890.00 +3.0/-1.0
Center Wavelength CWL Tolerance (nm): +3.0/-1.0
Full Width-Half Max FWHM (nm): 10.00 ±2
Full Width-Half Max FWHM Tolerance (nm): ±2
Minimum Transmission (%): >50
Operating Temperature (°C): -50 to +70
Coating: Traditional Coated
Surface Quality: 80-50
Thickness Tolerance (mm): ±0.1
Type: Bandpass Filter
Typical Applications: General Filtering
Blocking Wavelength Range (nm): 200 - Far IR
Construction: Mounted in Black Anodized Ring
Mount Thickness (mm): 5.9 ±0.1

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant