

8" x 10", ITO Coated EMI Shielded Plastic Window



Stock **#83-748** CLEARANCE 3-4 DAYS

- 1 + **£46.71**

ADD TO CART

Qty 1+
£46.71

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Bevel:
Protective as needed

Dimensions (mm):
203.20 x254.00

Dimensions (inches):
8.00 x 10.00 ±0.010

Thickness (mm):
1.27

Thickness (inches):
0.05 ±0.005

Coating: S1: BBAR (450-650nm) S2: ITO Coating
Coating Specification: Surface 1: R_{avg} <1% @ 450 - 650nm Surface 2: Clear Hard Coated
Construction: Silver Busbar Shielding Termination
Edges: Fine Ground
Substrate: PET
Type: Protective Window
Wavelength Range (nm): 450 - 650
Length (mm): 254.00
Width (mm): 203.20
Shielding Effectiveness @ 100MHz (dB): 49.00
Surface Resistivity (Ω/ Sq): 8.00
Visible Light Transmission VLT (%): >84

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View