

8" x 8" White Advanced Illumination Side-Fired Backlight

See More by [Advanced Illumination](#)



Stock **#88-508** 3-4 DAYS

-

1

+

£968.15

ADD TO CART

Qty 1+

£968.15

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color:
White

Model Number:
BX0808-WHI-IC

Operating Temperature (°C):
0 to 60

Dimensions (mm):

267.5 L x 267.5 W x 20.1 D
LED Lifetime (hours): 50,000
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Number of Channels: 1.00
Active Area (inches): 8 x 8
Type of Illumination: LED Illuminator
Manufacturer: Advanced Illumination
Geometry: Backlight
Illumination Mode: Constant

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Contains SVHC(s)