

900µm Aperture Diameter, Mounted, Precision Pinhole



900µm Aperture Diameter, Mounted, Precision Pinhole, #56-290

Stock **#56-290** 3-4 DAYS

⊖ 1 ⊕

£63.75

ADD TO CART

Qty 1-5
£63.75

Qty 6+
£56.27

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type: Mounted
Outer Diameter (mm): 25 +0.4/-0.000
Construction: Stainless Steel

Fixed Aperture Diameter (μm): 900
Thickness (mm): 0.03 Nominal
Aperture Tolerance (μm): ±5
Mount Thickness (mm): 1.25 ±0.05
Aperture Centration (μm): ±125

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant