

TECHSPEC® 9mm Dia. x 13.5mm FL VIS-EXT, Inked, Double-Convex Lens



Stock **#89-137-INK** [CONTACT US](#)

[Other Coating Options](#)

- 1 + **£45.05**

ADD TO CART

Qty 1-9
£45.05
Qty 10+
£40.59
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads
Diameter (mm): 9.00 ±0.025
Back Focal Length BFL (mm): 12.56

Effective Focal Length EFL (mm): 13.50
Coating: VIS-EXT (350-700nm)
Coating Specification: R _{avg} <0.5% @ 350 - 700nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 2.75
Center Thickness Tolerance (mm): ±0.05
Edge Thickness ET (mm): 1.2
Radius R₁=R₂ (mm): 13.46
Clear Aperture CA (mm): 8.1
f/#: 1.5
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.33
Type: Double-Convex Lens
Wavelength Range (nm): 350 - 700

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View