

TECHSPEC[®] 9mm Diameter x -12 FL, VIS 0°, Inked, Plano-Concave Lens



Stock **#48-342-INK** ☐ In Stock
[Other Coating Options](#)

-

1

+

£42.50

ADD TO CART

Qty 1-9
£42.50
Qty 10+
£38.25
Volume Pricing
Request Quote

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
9.00 ±0.025

Effective Focal Length EFL (mm):

-12.00
Substrate: NSF11
f#: 1.33
Numerical Aperture NA: 0.38
Coating: VIS 0° (425-675nm)
Type: Plano-Concave Lens
Wavelength Range (nm): 425 - 675
Back Focal Length BFL (mm): -13.26
Bevel: Protective bevel as needed
Center Thickness CT (mm): 2.25
Center Thickness Tolerance (mm): ±0.05
Centering (arcmin): <1
Clear Aperture CA (mm): 8.1
Coating Specification: Ravg ≤0.4% @ 425 - 675nm
Edge Thickness ET (mm): 3.24
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Radius R₁ (mm): -9.42
Surface Quality: 40-20
Damage Threshold, By Design: 5 J/cm² @ 532nm, 10ns
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View