

TECHSPEC® 9mm Uncoated, Amici Roof Prism



Amici Roof Prisms

Stock **#45-662** 3-4 DAYS

⊖ 1 ⊕ **£73.95**

ADD TO CART

Qty 1-5
£73.95

Qty 6+
£57.80

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Clear Aperture CA (mm):
8.00

Coating:
Uncoated

Substrate: □
[N-BK7](#)

Surface Quality: 60-40
Type: Amici Roof Prism
Dimensional Tolerance (mm): +0/-0.1
Angle Tolerance (arcmin): ±5
Resolution (arcsec): 6.00
Bevel: Protective bevel as needed
Image Orientation: Right-Handed
Ray Deviation (°): 90
Wavelength Range (nm): 350 - 2200
Surface Flatness (P-V): λ/2

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View
