

Achromatic Lens 6.25mm Dia. x 35mm FL, Uncoated



Stock #32-306 CLEARANCE **7 In Stock**

⊖ 1 ⊕ £10⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	£10.80 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Achromatic Lens **Type:**

Physical & Mechanical Properties

2.30 **Center Thickness CT 1 (mm):**

0.90 **Center Thickness CT 2 (mm):**

6.250000000 +0.00/-0.05 **Diameter (mm):**

2.86 **Edge Thickness ET (mm):**

±0.1 **Center Thickness Tolerance (mm):**

1.00 **Centering (arcmin):**

Optical Properties

33.59 **Back Focal Length BFL (mm):**

Uncoated **Coating:**

35.0000000000 **Effective Focal Length EFL (mm):**

[N-BK7 / N-SF5](#) **Substrate:**

0.0800000000 **Numerical Aperture NA:**

23.1400000000 **Radius R₁ (mm):**

-14.51 **Radius R₂ (mm):**

-38.86 **Radius R₃ (mm):**

40-20 **Surface Quality:**

±2 **Focal Length Tolerance (%):**

632.8 **Focal Length Specification Wavelength (nm):**

5.6 **f#:**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- Discounts up to 80% Off
- Quantities Extremely Limited
- Final Sale, No Returns

Shop the EO Mega Clearance presentations for the hottest deals on component-level products. Quickly browse the best optics, [imaging](#), and [photonics](#) deals you will ever see. Quantities are extremely limited and are sold on a first-come-first-serve basis.

Hurry, while supplies last. EO Mega Clearance products will never be sold again. Check out our standard [clearance products](#) for even more deals!

All products are final sale; EO will not accept returns. No additional information is available other than what is listed.

Compatible Mounts