

[All Products](#) / [Cameras](#) / [USB Cameras](#) / [Allied Vision Alvium Right Angle USB 3.1 Cameras](#)

[See all 127 Products in Family](#)

Allied Vision Alvium 1800 U-1242c, 1/1.1" 12.4MP C-Mount, Right Angle USB 3.1 Color Camera

See More by [Allied Vision](#)



Stock #19-596 3-4 DAYS

[Similar Cameras](#)

- 1 + **£1,348.10**

ADD TO CART

Qty 1+
£1,348.10

Volume Pricing
[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Video Output:
USB 3.1 Gen 1

Type: Color Camera
Manufacturer: Allied Vision
Mounting Threads: ¼-20 and M6 with Tripod Mount Adapter #14-156
Image Buffer: 256KB
Camera Family: Alvium Right Angle
Model Number: 1800 U-1242c
Imaging Sensor: Sony IMX545
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 1/1.1"
Resolution (MegaPixels): 12.40
Pixels (H x V): 4,128 x 3,008
Pixel Size, H x V (µm): 2.74 x 2.74
Sensing Area, H x V (mm): 11.3 x 8.2
Frame Rate (fps): 28.00
Pixel Depth: 8/10/12 bit
Exposure Time: 160µs - 10s @ 450 MBps 168µs - 10s @ 200 MBps
Connector: USB 3.1 Gen 1, Micro-B
Power Supply: Power over USB or via GPIO
Power Consumption (W): 3.4
GPIOs: 4 Programmable TTL GPIOs
Synchronization: Hardware Trigger (GPIO) or Software Trigger
Dimensions (mm): 38 x 32 x 29 (includes connectors and lens mount)
Weight (g): 70
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel (Right Angle)
Dynamic Range (dB): Not Specified
Operating Temperature (°C): +5 to +65
Storage Temperature (°C): -10 to +70
GPIO Connector Type: 7-pin JST
Machine Vision Standard: USB3 Vision v1.0, GenICam

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant

