

Allied Vision Alvium G5-508m, 2/3" 5.1MP C-Mount, 5GigE PoE Monochrome Camera (Recertified 05-P)

See More by [Allied Vision](#)



Stock **#23-623-RCD-05P** RECERTIFIED **1 In Stock**

-

1

+

£1,178⁷¹

ADD TO CART

Volume Pricing	
Qty 1+	£1,178.71 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Monochrome Camera	Type:
Avium G5-508m	Model Number:
Allied Vision	Manufacturer:
Avium G5	Camera Series:
Monochrome	Spectrum:

Physical & Mechanical Properties

60 × 29 × 29	Dimensions (mm):
100	Weight (g):
Full	Housing:

Sensor

512KB	Image Buffer:
2/3"	Sensor Format:
5.10	Resolution (Megapixels):
95.00	Frame Rate (fps):
2,464 x2,056	Pixels (H x V):
3.45 x3.45	Pixel Size, H x V (µm):
8.50 x7.10	Sensing Area, H x V (mm):
Sony IMX250	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Global	Shutter Type:
8/10/12 Bit	Pixel Depth:
24 µs to 10 s	Exposure Time:
Not Specified	Dynamic Range (dB):
GigE Vision V1.2, GenICam V2.0	Machine Vision Standard:

Electrical

External power: 6.1 W at 12 VDC Power over Ethernet: 7.0 W	Power Consumption (W):
--	------------------------

Hardware & Interface Connectivity

5GigE (PoE)	Interface:
5GigE, RJ45 with Screw Locks	Connector:
PoE, 12 to 24 VDC via GPIO, or with external power supply#23-581	Power Supply:
1 opto-isolated input, 1 opto-isolated output, 2 non-isolated GPIOs	GPIOs:
Hardware Trigger (GPIO) or Software Trigger	Synchronization:
Back Panel	Interface Port Orientation:
10-pin TFM	GPIO Connector Type:

Threading & Mounting

C-Mbunt	Mount:
---------	--------

Mounting Threads:
1/4"-20 and M6 with Tripod Mount Adapter [#14-156](#)

Environmental & Durability Factors

+5 to +60	Operating Temperature (°C):
-20 to +85	Storage Temperature (°C):

Regulatory Compliance

View	Certificate of Conformance:
----------------------	-----------------------------

PRODUCT DETAILS

- 4.2 Times More Bandwidth than GigE
- Up to 24.6MP Resolution with Framerates up to 691 FPS
- Onboard Image Processing and Expansive Feature Sets

Allied Vision Alvium G5 5GigE PoE Cameras feature a lightweight, compact form factor and combines the advantages of the established 5GigE Vision standard with the flexibility of the Alvium platform. Powered by ALVUM® Technology, the sugar cube style camera delivers high image quality at a low power consumption. These cameras feature the latest industrial standard hardware and can easily be integrated into any USB3 Vision or GigE Vision system while ensuring long-term availability and reliability. With precision sensor alignment, enhanced cleanliness, fixed pattern noise correction, and defect pixel correction, resolutions up to 24.6MP and framerates up to 691 FPS are available. Allied Vision Alvium G5 5GigE PoE Cameras feature a gigabit ethernet port on the back panel and are available in a variety of monochrome and color options with either C-Mount or S-Mount lens interfaces all in the compact sugar cube format.