

# Allied Vision Mako G-234C 1/1.2" Color CMOS Camera

See More by [Allied Vision](#)



Allied Vision Mako Power over Ethernet (PoE) Cameras (Front)



Stock **#34-200** 3-4 DAYS

[Similar Cameras](#)



1



£714.00

ADD TO CART

Qty 1+

£714.00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

**Note:** This item requires accessories for use | [Learn More](#)

Get Product Downloads

**Video Output:**  
GigE (PoE)

**Type:**  
Color Camera

|                                                                                            |
|--------------------------------------------------------------------------------------------|
| <b>Manufacturer:</b><br>Allied Vision                                                      |
| <b>Mounting Threads:</b><br>¼-20 with Tripod Mount Adapter <a href="#">#88-483</a>         |
| <b>Image Buffer:</b><br>64MB                                                               |
| <b>Camera Family:</b><br>Mako                                                              |
| <b>Model Number:</b><br>G-234C                                                             |
| <b>Imaging Sensor:</b><br>Sony IMX249                                                      |
| <b>Type of Sensor:</b><br>Progressive Scan CMOS                                            |
| <b>Type of Shutter:</b><br>Global                                                          |
| <b>Camera Sensor Format:</b><br>1/1.2"                                                     |
| <b>Resolution (MegaPixels):</b><br>2.35                                                    |
| <b>Pixels (H x V):</b><br>1,936 x 1,216                                                    |
| <b>Pixel Size, H x V (µm):</b><br>5.86 x 5.86                                              |
| <b>Sensing Area, H x V (mm):</b><br>11.34 x 7.13                                           |
| <b>Frame Rate (fps):</b><br>40.00                                                          |
| <b>Pixel Depth:</b><br>10/12 bit                                                           |
| <b>Exposure Time:</b><br>Auto Exposure                                                     |
| <b>Connector:</b><br>GigE, RJ45 with Screw Locks                                           |
| <b>Power Supply:</b><br>Power over Ethernet (PoE), via GPIO, or with external power supply |
| <b>Power Consumption (W):</b><br>2.4 (12VDC External Power Supply)<br>2.8 (PoE)            |
| <b>GPIOs:</b><br>1 opto-isolated input, 3 opto-isolated ouputs                             |
| <b>Synchronization:</b><br>Hardware Trigger (GPIO), Software Trigger, or PTP (IEEE 1588)   |
| <b>Dimensions (mm):</b><br>42.6 x 29.2 x 29.2 (excludes connectors and lens mount)         |
| <b>Weight (g):</b><br>80                                                                   |
| <b>Mount:</b><br>C-Mount                                                                   |
| <b>Housing:</b><br>Full                                                                    |
| <b>Interface Port Orientation:</b><br>Back Panel                                           |
| <b>Dynamic Range (dB):</b><br>73.6                                                         |
| <b>Operating Temperature (°C):</b><br>+5 to +45                                            |
| <b>Storage Temperature (°C):</b><br>-10 to +70                                             |
| <b>GPIO Connector Type:</b><br>8-pin Hirose (HR25)                                         |
| <b>Machine Vision Standard:</b><br>GigE Vision V1.2, GenICam SFNC V1.2.1                   |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |

