

Allied Vision Manta G-033 1/2" Color CCD Camera

⊖ 1 ⊕ £468^{.00}

Volume Pricing	
Qty 1+	£468.00 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General

Type: Color Camera

Manta G-033C	Model Number:
Allied Vision	Manufacturer:
Manta	Camera Series:

Physical & Mechanical Properties

71 x44 x29 (excludes connectors and lens mount)	Dimensions (mm):
200	Weight (g):
Full	Housing:

Sensor

32MB	Image Buffer:
1/2"	Sensor Format:
0.30	Resolution (Megapixels):
88.70	Frame Rate (fps):
656 x492	Pixels (H x V):
9.9 x9.9	Pixel Size, H x V (µm):
6.5 x4.9	Sensing Area, H x V (mm):
Sony ICX414	Imaging Sensor:
Progressive Scan CCD	Type of Sensor:
Global	Shutter Type:
12 bit	Pixel Depth:
Via Software	Exposure Time:
61.9	Dynamic Range (dB):
GigE Vision v1.2, GenICam SFNC V1.2.1	Machine Vision Standard:

Electrical

3.6 (12VDC External Power Supply)	Power Consumption (W):
-----------------------------------	------------------------

Hardware & Interface Connectivity

GigE	Interface:
GigE, RJ45 with Screw Locks	Connector:
Power Supply Required and Sold Separately. USA: #15-281 Europe: #15-281 Japan: #15-281 China: #15-281	Power Supply:
2 opto-isolated inputs, 2 opto-isolated outputs	GPIOs:
Hardware Trigger (GPIO) or Software Trigger	Synchronization:
Back Panel	Interface Port Orientation:
12-pin Hirose (HR10)	GPIO Connector Type:

Threading & Mounting

C-Mount	Mount:
1/4-20 with Tripod Mount Adapter #89-996	Mounting Threads:

Environmental & Durability Factors

	Operating Temperature (°C):
--	-----------------------------

+5 to +45	
	Storage Temperature (°C):
-10 to +70	

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:

Product Details

- Ideal Analog Replacement
- Up to 1" Maximum Sensors
- Up to 125 fps
- 32MB of Onboard Memory

Allied Vision Manta GigE Cameras are an excellent choice for entry into using the GigE interface. Featuring an intuitive user interface as well as a powerful SDK, these cameras are an excellent value. With options from 0.3 MegaPixels to 12 MegaPixels, all sensors offered cover a wide array of applications. Allied Vision Manta GigE Cameras feature sensors from 1/4" to 1" in size. GigE Cable and Power Supply, both sold separately, are required for operation. Additional [GigE cables](#), [#89-996](#) 1/4-20 Mounting Plate, and [#62-712](#) 12 Pin I/O Cable are available.