

[See all 24 Products in Family](#)

## Allied Vision Manta G-040 1/2.9" Color CMOS Camera

See More by [Allied Vision](#)



Allied Vision Manta GigE Cameras (Front)



Stock **#11-607** [CONTACT US](#)

[Similar Cameras](#)

- 1 + £560<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	£560.00 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

**Note:** This item requires accessories for use | [Learn More](#)

### Product Downloads

Color

Spectrum:

### General

Type:

Color Camera

Manta G-040C

**Model Number:**

Allied Vision

**Manufacturer:**

Manta

**Camera Series:**

## Physical & Mechanical Properties

**Dimensions (mm):**  
71 x 44 x 29 (excludes connectors and lens mount)

**Weight (g):**  
190

**Housing:**  
Full

## Sensor

**Image Buffer:**  
128MB

**Sensor Format:**  
1/2.9"

**Resolution (Megapixels):**  
0.40

**Frame Rate (fps):**  
286.00

**Pixels (H x V):**  
728 x 544

**Pixel Size, H x V (µm):**  
6.9 x 6.9

**Sensing Area, H x V (mm):**  
4.96 x 3.72

**Imaging Sensor:**  
Sony IMX287

**Type of Sensor:**  
Progressive Scan CMOS

**Shutter Type:**  
Global

**Pixel Depth:**  
12 bit

**Exposure Time:**  
Via Software

**Dynamic Range (dB):**  
74.3

**Machine Vision Standard:**  
GigE Vision v1.2, GenICam SFNC V1.2.1

## Electrical

**Power Consumption (W):**  
2.77 (12VDC External Power Supply)

## Hardware & Interface Connectivity

**Interface:**  
GigE

**Connector:**  
GigE, RJ45 with Screw Locks

**Power Supply:**  
Power Supply Required and Sold Separately:  
USA: [#15-281](#)  
Europe: [#15-281](#)  
Japan: [#15-281](#)  
China: [#15-281](#)

**GPIOs:**  
2 opto-isolated inputs, 2 opto-isolated outputs

**Synchronization:**  
Hardware Trigger (GPIO) or Software Trigger

**Interface Port Orientation:**  
Back Panel

**GPIO Connector Type:**  
12-pin Hirose (HR10)

## Threading & Mounting

**Mount:**  
C-Mount

**Mounting Threads:**  
1/4-20 with Tripod Mount Adapter [#89-996](#)

## Environmental & Durability Factors

---

+5 to +45      **Operating Temperature (°C):**

-10 to +70      **Storage Temperature (°C):**

---

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

---

**Reach 240:**  
[Compliant](#)

---

## Product Details

- Ideal Analog Replacement
- Up to 1" Maximum Sensors
- Up to 125 fps
- 32MB of Onboard Memory

Allied Vision Manta GigE Cameras are an excellent choice for entry into using the GigE interface. Featuring an intuitive user interface as well as a powerful SDK, these cameras are an excellent value. With options from 0.3 MegaPixels to 12 MegaPixels, all sensors offered cover a wide array of applications. Allied Vision Manta GigE Cameras feature sensors from 1/4" to 1" in size. GigE Cable and Power Supply, both sold separately, are required for operation. Additional [GigE cables](#), [#89-996](#) 1/4-20 Mounting Plate, and [#62-712](#) 12 Pin I/O Cable are available.

---