

Basic Liquid Crystal Controller



Stock **#63-045** CLEARANCE 3-4 DAYS

-

1

+

£594.96

ADD TO CART

Qty 1+

£594.96

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Dimensions (inches):
7.0 x 5.0 x 3.1

Weight (lbs):
2.00

Power Requirement:
115/230 V, 50/60 Hz, 5 W

Output Voltage (V):
2kHz AC square λ adjustable 0-25V RMS; 50% duty cycle, minimal DC bias

Voltage Resolution:

3mV

Modulation:

Internal: 0.7-150Hz

TTL input: 12V maximum DC-1 kHz

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Reach 209:

[Compliant](#)

Certificate of Conformance:

[View](#)