

Basler ace acA2500-60uc Color USB 3.0 Camera

See More by [Basler](#)



Basler ace USB 3.0 Cameras (Front)



Stock #35-930 **1 In Stock**

- 1 + £864⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£864.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

Color **Spectrum:**

General

Color Camera **Type:**

acA2500-60uc **Model Number:**

Basler **Manufacturer:**

ace **Camera Series:**

Physical & Mechanical Properties

Dimensions (mm):
29.3 x 29 x 29 (excludes connectors and lens mount)

Weight (g):
80

Housing:
Full

Sensor

Image Buffer:
Not Specified

Sensor Format:
1"

Resolution (Megapixels):
5.00

Frame Rate (fps):
60.00

Pixels (H x V):
2,590 x 2,048

Pixel Size, H x V (µm):
4.8 x 4.8

Sensing Area, H x V (mm):
12.43 x 9.83

Imaging Sensor:
ON Semi PYTHON 5000

Type of Sensor:
Progressive Scan CMOS

Shutter Type:
Global

Pixel Depth:
10 bit

Exposure Time:
Programmable via camera API, hardware trigger

Dynamic Range (dB):
Not Specified

Machine Vision Standard:
USB3 Vision v1.0

Electrical

Power Consumption (W):
3.5

Hardware & Interface Connectivity

Interface:
USB 3.0

Connector:
USB 3.0, Micro-B with Screw Locks

Power Supply:
Power over USB

GPIOs:
1 opto-coupled input line, 1 opto-coupled output line,
2 general purpose I/O (GPIO) lines

Synchronization:
Hardware Trigger (GPIO), Software Trigger, or Free-Run

Interface Port Orientation:
Back Panel

GPIO Connector Type:
6-pin Hirose (HR10)

Threading & Mounting

Mount:
C-Mount

Mounting Threads:
1/4-20 with Tripod Mount Adapter [#88-517](#)

Environmental & Durability Factors

Operating Temperature (°C):
0 to +50

Storage Temperature (°C):
-20 to +80

Regulatory Compliance

[Compliant](#)

RoHS 2015:

[View](#)

Certificate of Conformance:

[Compliant](#)


Reach 235:

Product Details

- High Speed USB 3.0 Interface
- Ultra-Small Form Factor
- Fully USB3 Vision Compliant

Basler ace USB 3.0 Cameras are an ideal choice for analog camera users looking to upgrade to digital, or for FireWire or USB 2.0 users looking for faster data transfer rates. Basler ace USB 3.0 Cameras are fully USB3 Vision compliant and feature a small, 29 x 29mm form factor that makes them easy drop-in replacements for many analog, FireWire, or USB 2.0 cameras. Additionally, these USB 3.0 cameras feature screw-locking USB 3.0 ports for increased ruggedness in demanding applications, such as factory floor use. All cameras include the Basler Pylon SDK software and driver.

Technical Information



MT9P031 Sensor QE Curve