

Basler ace2 a2A1920-160umPRO Monochrome USB3 Pro Camera



Basler ace2 USB 3.0 Cameras (Front)



Stock **#16-629** [CONTACT US](#)

[Similar Cameras](#)



1



£407.15

ADD TO CART

Qty 1+

£407.15

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Video Output:
USB 3.0

Type:
Monochrome Camera

Manufacturer:
Basler

Mounting Threads: ¼-20 with Tripod Mount Adapter #16-641
Image Buffer: Not Specified
Camera Family: ace2
Model Number: a2A1920-160umPRO
Imaging Sensor: Sony IMX392
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 1/2.3"
Resolution (MegaPixels): 2.00
Pixels (H x V): 1,920 x 1,200
Pixel Size, H x V (µm): 3.45 x 3.45
Sensing Area, H x V (mm): 6.6 x 4.1
Frame Rate (fps): 160.00
Pixel Depth: 8/10/12 bit
Exposure Time: Freely Programmable
Connector: USB 3.0, Micro-B
Power Supply: Power over USB
Power Consumption (W): 4.3
GPIOs: 1 opto-coupled input line, 2 general purpose I/O (GPIO) lines
Synchronization: Hardware Trigger (GPIO), Software Trigger, or Free-Run
Dimensions (mm): 36.3 x 29 x 29 (excludes connectors and lens mount)
Weight (g): <90
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): 71.7
Operating Temperature (°C): -10 to +60
Storage Temperature (°C): -20 to +80
GPIO Connector Type: 6-pin MB
Machine Vision Standard: USB3 Vision v1.0, GenICam

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant