

# SCHOTT BG25, 25.4mm Dia., 3mm Thick, Colored Glass Bandpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#84-901** 3-4 DAYS

-

1

+

**£39.95**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-10                      |
| £39.95                        |
| Qty 11+                       |
| £34.85                        |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):  
25.40

Center Wavelength CWL (nm):  
400.00

|                                                                            |
|----------------------------------------------------------------------------|
| <b>Density (g/cm³):</b><br>2.56                                            |
| <b>Glass/Filter Number:</b><br><a href="#">SCHOTT BG25</a>                 |
| <b>Coating:</b><br>Uncoated                                                |
| <b>Color:</b><br>Blue-Violet                                               |
| <b>Surface Quality:</b><br>80-50                                           |
| <b>Thickness (mm):</b><br>3.00 ±0.2                                        |
| <b>Type:</b><br>Bandpass Filter                                            |
| <b>Wavelength:</b><br>UV-VIS                                               |
| <b>Note:</b><br>Intense UV radiation can cause a reduction in transmission |
| <b>Bevel:</b><br>Protective as needed                                      |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Exempt</a>                |
| <b>Reach 224:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |

---