

TECHSPEC[®] 30mm, C-Mount Ring Mount, M6 Tapped Hole



Stock **#63-977** 20+ In Stock

-

1

+

£88^{.00}

ADD TO CART

Volume Pricing	
Qty 1-4	£88.00 each
Qty 5-9	£77.92 each
Qty 10-25	£72.16 each
Need More?	Request Quote

!

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Post Mounting Adapter

Function:

Physical & Mechanical Properties

12.70

Thickness (mm):

Black Anodized Aluminum (6061 T6)

Construction:

48.0	Outer Diameter (mm):
30.0	Inner Diameter (mm):
Threading & Mounting	
21.75	Mounting Flat to Center (mm):
C-Mount	Thread Type:
M6 x 1.0	Compatible Post:

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Allow for Post Mounting C, S, and T-Mount Tube System Assemblies
- 1/4-20 or M6 Tapped Mounting Options
- Black Anodized Aluminum Construction

TECHSPEC® C, S, and T-Mount Ring Mounts feature a screw closure and accept 30mm, 16mm, and 48mm outer diameter tubes and barrels, respectively. Ring mounts are available with either 1/4-20 or M6 tapped mounting threads with a flat mounting surface to facilitate mounting to optical bench posts. These mounts are compatible with a wide variety of Edmund Optics optomechanical components utilizing C, S, or T-Mount threads. TECHSPEC C, S, and T-Mount Ring Mounts are ideal for quickly integrating C, S, or T-Mount tube assemblies into any benchtop system. A black anodized construction reduces reflections within a system.

Technical Information

