

TECHSPEC®

C-Mount Achromat Pair 1:1 with 30 and 30mm Focal Lengths



Stock **#87-185**

3-4 DAYS

-

1

+

£314.50

ADD TO CART

Qty 1-5

£314.50

Qty 6+

£251.60

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Quality:
40-20

Working f#:
f//1.4 - f//37

Coating:
VS 0° (425-675nm)

Coating Specification:

R _{avg} ≤0.4% @ 425 - 675nm
Aperture (mm): 0.8 - 20
Effective Focal Length EFL A (mm): 30.0
Effective Focal Length EFL B (mm): 30.0
Housing Diameter (mm): 38.00
Housing Length (mm): 45.9
Magnification: 1:1
Object Distance (mm): 15.00
Image Distance (mm): 13.00
Type: Relay Lens
Wavelength Range (nm): 425 - 675

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View